

# BRY4100C7W Cut Sheet



Bryant watertight pin and sleeve connector, 100A, 480 VAC, 3-phase, 3-pole, 4-wire, 7 hour, accepts cord size 0.905-1.68in, IP67, nylon housing, red.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY4100C7W>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Connector
<b>Application</b>	Watertight
<b>Wiring Device Type</b>	Pin and sleeve
<b>With Cap</b>	No
<b>Amperage Rating</b>	100A
<b>Voltage Rating</b>	480 VAC
<b>Number of Phases</b>	3
<b>Number of Poles</b>	3

<b>Number of Wires</b>	4
<b>Wire Size</b>	4-1 AWG
<b>Configuration</b>	7 hour
<b>Cord Diameter</b>	0.905-1.68in
<b>IP Rating</b>	IP67
<b>Housing Material</b>	Nylon
<b>Color</b>	Red
<b>Manufacturer Part Number</b>	C4100C7WA

## Agency Approvals

<b>UL Listed File #</b>	E146033
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	N/A
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/BRY4100C7W.pdf>  
See store item page for other formats.