

BRY420MI9W Cut Sheet



Bryant pin and sleeve mechanical interlock, rotary, enclosed, load break capable, 240 VAC, 20A, 3-phase, 3-pole, 4-wire, 9 hour pin and sleeve receptacle, 10kA SCCR, 10.1in x6.9in x7.8in housing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY420MI9W>

Technical Specifications

| | |
|---------------------------|-------------------------------------|
| Brand | Bryant |
| Item | Pin and sleeve mechanical interlock |
| Handle Type | Rotary |
| Body Type | Enclosed |
| Fusible | No |
| Load Break Capable | Yes |
| Number of Poles | 3 |
| Voltage Rating | 600 VAC |
| Amperage Rating | 20A |

| | |
|-------------------------------|---|
| SCCR Rating | 10kA SCCR |
| Connection | 3-phase, 3-pole, 4-wire, 9 hour pin and sleeve receptacle |
| Mounting | Wall |
| UL Rating | UL 508 rated |
| Housing Size | 10.1in x6.9in x7.8in |
| Includes | Watertight conduit hub and grounding plate |
| Additional Information | Lockout/tagout capable. Suitable as motor disconnect |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E70402 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 033196_C_00 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BRY420MI9W.pdf>
See store item page for other formats.