

# BRY5466NP Cut Sheet



Bryant industrial heavy duty straight blade plug, 20A, 250 VAC, 1-phase, 2-pole, 3-wire, NEMA 6-20, accepts cord size 0.3-0.65in, nylon housing, black and white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY5466NP>

## Technical Specifications

Brand	Bryant
Item	Plug
Application	Industrial heavy duty
Blade Type	Straight
With Cap	No
Self-grounding	No
Amperage Rating	20A
Voltage Rating	250 VAC
Number of Phases	1

Number of Poles	2
Number of Wires	3
Wire Size	18-10 AWG
Copper Wire Only	No
Configuration	NEMA 6-20
Cord Diameter	0.3-0.65in
Housing Material	Nylon
Color	Black and white

## Agency Approvals

UL Listed File #	E1381
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	016215
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BRY5466NP.pdf>  
See store item page for other formats.