

# BRY5662 Cut Sheet



Bryant industrial heavy duty duplex straight blade receptacle, 15A, 250 VAC, 1-phase, 2-pole, 3-wire, NEMA 6-15, nylon molded housing, brown.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BRY5662>

## Technical Specifications

<b>Brand</b>	Bryant
<b>Item</b>	Receptacle
<b>Application</b>	Industrial heavy duty
<b>Receptacle Type</b>	Duplex
<b>Blade Type</b>	Straight
<b>With Cap</b>	No
<b>Self-grounding</b>	Yes
<b>Amperage Rating</b>	15A
<b>Voltage Rating</b>	250 VAC
<b>Number of Phases</b>	1
<b>Number of Poles</b>	2
<b>Number of Wires</b>	3
<b>Wire Size</b>	14-10 AWG
<b>Copper Wire Only</b>	Yes
<b>Configuration</b>	NEMA 6-15
<b>Housing Material</b>	Nylon molded
<b>Color</b>	Brown

## Agency Approvals

<b>UL Listed File #</b>	E2258
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	016215
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>