BRYDS60SS Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Bryant TECH-SPEC series disconnect switch, enclosed, 3-pole, 600 VAC, 60A, 65 kA SCCR, wall mount, UL 60947–1 rated, front operated, 10.3 x 7.3 x 5.93in housing. (2) conduit hubs included.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/BRYDS60SS

Technical Specifications

Brand	Bryant
Item	Disconnect switch
Series	TECH-SPEC
Body Type	Enclosed
Load Break Capable	Yes
Fusible	No
Number of Poles	3
Voltage Rating	600 VAC
Amperage Rating	60A
SCCR Rating	65 kA SCCR

Horsepower Rating	15 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	10.3 x 7.3 x 5.93in
Housing Material	304 stainless steel
Housing Rating	NEMA 4X/12 (IP69K)
UL Rating	UL 60947–1 rated
Includes	(2) conduit hubs

Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/BRYDS60SS.pdf
See store item page for other formats.