BRYDS60VFD Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



Bryant TECH-SPEC series disconnect switch, enclosed, 3-pole, (1) N.O. early break auxiliary contacts, 600 VAC, 60A, 10 kA SCCR, wall mount, UL 60947–1 rated, front operated, 9.9 x 6.87 x 5.94in housing. (2) conduit hubs and (4) mounting feet included.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/BRYDS60VFD

Technical Specifications

Brand	Bryant
Item	Disconnect switch
Series	TECH-SPEC
Body Type	Enclosed
Load Break Capable	Yes
Fusible	No
Number of Poles	3
Auxiliary Contacts	(1) N.O. early break
Voltage Rating	600 VAC
Amperage Rating	60A

SCCR Rating	10 kA SCCR
Horsepower Rating	25 hp
Configuration	Front operated
Handle Type	Rotary
Mounting	Wall
Housing Size	9.9 x 6.87 x 5.94in
Housing Material	Thermoplastic
Housing Rating	NEMA 4X/12 (IP69K)
UL Rating	UL 60947–1 rated
Includes	(2) conduit hubs and (4) mounting feet

Agency Approvals

UL Listed File #	E70402
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/BRYDS60VFD.pdf
See store item page for other formats.