

BSEM-E7-PG29T-WCL Cut Sheet



Bimed EMC cable gland, PG29 thread type, nickel-plated brass, accepts 16 to 25mm diameter cable, IP68. Package of 5. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BSEM-E7-PG29T-WCL>

Technical Specifications

Brand	Bimed
Item	Cable gland
Application	EMC
Thread Type	PG29
Material	Nickel-plated brass
Cable OD Range	16 to 25mm
Shield OD Range	12 to 20mm
IP Rating	IP68
Strain Relief	No
Quantity per Pack	5
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes with Exemptions (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BSEM-E7-PG29T-WCL.pdf>
See store item page for other formats.