

BSEM-E9-PG42T-WCL Cut Sheet



Bimed EMC cable gland, PG42 thread type, nickel-plated brass, accepts 30 to 38mm diameter cable, IP68. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BSEM-E9-PG42T-WCL>

Technical Specifications

Brand	Bimed
Item	Cable gland
Application	EMC
Thread Type	PG42
Material	Nickel-plated brass
Cable OD Range	30 to 38mm
Shield OD Range	26 to 34mm
IP Rating	IP68
Strain Relief	No
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes with Exemptions (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/BSEM-E9-PG42T-WCL.pdf>
See store item page for other formats.