

BSSPX-12-W Cut Sheet



Bimed cable gland, PG9 thread type, polyamide, light gray, accepts 4 to 8mm diameter cable, IP68, with strain relief. Package of 5. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BSSPX-12-W>

Technical Specifications

| | |
|--------------------------|-------------------|
| Brand | Bimed |
| Item | Cable gland |
| Thread Type | PG9 |
| Material | Polyamide |
| Color | Light gray |
| Cable OD Range | 4 to 8mm |
| IP Rating | IP68 |
| Strain Relief | Yes |
| Quantity per Pack | 5 |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E199260 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 190896 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BSSPX-12-W.pdf>
See store item page for other formats.