

BSSPX-12-W Cut Sheet



Bimed cable gland, PG9 thread type, polyamide, light gray, accepts 4 to 8mm diameter cable, IP68, with strain relief. Package of 5. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BSSPX-12-W>

Technical Specifications

Brand	Bimed
Item	Cable gland
Thread Type	PG9
Material	Polyamide
Color	Light gray
Cable OD Range	4 to 8mm
IP Rating	IP68
Strain Relief	Yes
Quantity per Pack	5
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	E199260
UL Hazardous File #	None
CE	View CE declarations
CSA File #	190896
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document