

# BSV-24P-D Cut Sheet



Patlite audible alarm, 85 dB at 1m, 246 Hz to 2.9 kHz tone frequency, (15) selectable tone(s), 12-24 VDC, panel or surface mount, polycarbonate housing, dark gray, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BSV-24P-D>

---

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Audible alarm
<b>Loudness Decibel</b>	85 dB at 1m
<b>Tone Frequency</b>	246 Hz to 2.9 kHz
<b>Tone Type</b>	(15) selectable
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	12-24 VDC
<b>Mounting</b>	Panel or surface
<b>Housing Material</b>	Polycarbonate
<b>Color</b>	Dark gray
<b>IP Rating</b>	IP54

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	S24210
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>