

BSV-24P-W Cut Sheet



Patlite audible alarm, 85 dB at 1m, 246 Hz to 2.9 kHz tone frequency, (15) selectable tone(s), 12-24 VDC, panel or surface mount, polycarbonate housing, off-white, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BSV-24P-W>

Technical Specifications

Brand	Patlite
Item	Audible alarm
Loudness Decibel	85 dB at 1m
Tone Frequency	246 Hz to 2.9 kHz
Tone Type	(15) selectable
Touch to Acknowledge	No
Voltage Rating	12-24 VDC
Mounting	Panel or surface
Housing Material	Polycarbonate
Color	Off-white
IP Rating	IP54

Agency Approvals

UL Listed File #	None
UL Recognized File #	S24210
UL Hazardous File #	None
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document