

BW125JAGU-3P075SB Cut Sheet



Fuji Electric molded case circuit breaker, 125A frame, 75A, 600 VAC / 250 VDC, 3-pole, characteristics, thermal magnetic, 30kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and terminal covers included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW125JAGU-3P075SB>

Technical Specifications

Brand	Fuji Electric	Trip Curve	Characteristics
Item	Circuit breaker	Trip Type	Thermal magnetic
Circuit Breaker Type	Molded case	Interrupting Rating	30kA @ 480 VAC
Circuit Type	Feeder and branch	UL Rating	UL 489 listed
Current-Limiting	No	Mounting	Panel
Frame Size	125A frame	HACR Rated	No
Amperage Rating	75A	Reverse Feed Capable	Yes
Voltage Rating	600 VAC / 250 VDC	Includes	Line and load lug terminals and terminal covers
Number of Poles	3		

Agency Approvals

UL Listed File #	E90584
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BW125JAGU-3P075SB.pdf>
See store item page for other formats.