

BW250JAGU-3P150SB Cut Sheet



Fuji Electric molded case circuit breaker, 250A frame, 150A, 600 VAC / 250 VDC, 3-pole, characteristics, thermal magnetic, 30kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and terminal covers included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW250JAGU-3P150SB>

Technical Specifications

| | |
|-----------------------------|---|
| Brand | Fuji Electric |
| Item | Circuit breaker |
| Circuit Breaker Type | Molded case |
| Circuit Type | Feeder and branch |
| Current-Limiting | No |
| Frame Size | 250A frame |
| Amperage Rating | 150A |
| Voltage Rating | 600 VAC / 250 VDC |
| Number of Poles | 3 |
| Trip Curve | Characteristics |
| Trip Type | Thermal magnetic |
| Interrupting Rating | 30kA @ 480 VAC |
| UL Rating | UL 489 listed |
| Mounting | Panel |
| HACR Rated | No |
| Reverse Feed Capable | Yes |
| Includes | Line and load lug terminals and terminal covers |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E90584 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |