

BW630RAGU-3P500SB Cut Sheet



Fuji Electric molded case circuit breaker, 630A frame, 500A, 480 VAC / 250 VDC, 3-pole, characteristics, thermal magnetic, 50kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW630RAGU-3P500SB>

Technical Specifications

Brand	Fuji Electric
Item	Circuit breaker
Circuit Breaker Type	Molded case
Circuit Type	Feeder and branch
Current-Limiting	No
Frame Size	630A frame
Amperage Rating	500A
Voltage Rating	480 VAC / 250 VDC
Number of Poles	3
Trip Curve	Characteristics
Trip Type	Thermal magnetic
Interrupting Rating	50kA @ 480 VAC
UL Rating	UL 489 listed
Mounting	Panel
HACR Rated	No
Reverse Feed Capable	Yes
Includes	Line and load lug terminals

Agency Approvals

UL Listed File #	E90584
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document