

BW9FHA-R Cut Sheet



Fuji Electric field installable shunt trip, left side mount, 24-48 VAC/VDC coil voltage, 19.69in 20AWG lead wires. For use with Fuji Electric 400A, 630A and 800A frame MCCBs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW9FHA-R>

Technical Specifications

Brand	Fuji Electric
Item	Shunt trip
Field Installable	Yes
Mounting	Left side
Coil Voltage	24-48 VAC/VDC
Connection	19.69in 20AWG lead wires
For Use With	Fuji Electric 400A, 630A and 800A frame MCCBs

Agency Approvals

UL Listed File #	E93289
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BW9FHA-R.pdf>
See store item page for other formats.