

BW9V0JA Cut Sheet



Fuji Electric rotary handle, pistol, black, external front mount, 2-position, lockable in OFF only, defeatable, IP54. For use with Fuji Electric 630A and 800A frame MCCBs. 0.4in shaft and operator included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BW9V0JA>

Technical Specifications

Brand	Fuji Electric
Item	Handle
Handle Type	Rotary
Handle Style	Pistol
Color	Black
Mounting	External front
Number Of Positions	2
Lockable Positions	OFF only
Defeatable	Yes
IP Rating	IP54
For Use With	Fuji Electric 630A and 800A frame MCCBs
Includes	0.4in shaft and operator
Additional Information	Purchase separately, optional shaft BZ-VS2 for 9.843in maximum mounting depth

Agency Approvals

UL Listed File #	E93289
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BW9V0JA.pdf>
See store item page for other formats.