

# BX-04AD-2B Cut Sheet



BRX analog input module, 4-channel, voltage, 16-bit, external 24 VDC required. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-04AD-2B>

## Technical Specifications

<b>Brand</b>	BRX
<b>Item</b>	Input module
<b>I/O Module Type</b>	Analog
<b>Number Of Input Channels</b>	4
<b>Input Signal Type(s)</b>	Voltage
<b>Isolated Channels</b>	No
<b>Number of Non-Isolated Input Commons</b>	1

<b>Input Resolution</b>	16-bit
<b>Input Voltage Signal Range</b>	0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
<b>External Power Requirement</b>	24 VDC
<b>Requires</b>	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
<b>Programming Software</b>	Do-more Designer programming software v2.3 or later

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BX-04AD-2B.pdf>  
See store item page for other formats.