

# BX-04DA-1 Cut Sheet



BRX analog output module, 4-channel, current, 16-bit, output current signal range(s) of 0-20 mA and 4-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-04DA-1>

## Technical Specifications

Brand	BRX
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	4
Output Signal Type	Current
Analog Output Type	Sourcing
Isolated Channels	No
Number of Non-Isolated Output Commons	1
Output Resolution	16-bit
Output Current Signal Range	0-20 mA and 4-20 mA
External Power Requirement	24 VDC
Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.3 or later

## Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>