

BX-04THM Cut Sheet



BRX temperature input module, thermocouple, 4-channel, 16-bit resolution, input thermocouple type(s): J, E, K, R, S, T, B, N, C. (1) BX-RTB10 screw terminal block kit included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-04THM>

Technical Specifications

Brand	BRX
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermocouple
Number Of Input Channels	4
Input Thermocouple Signal Type	J, E, K, R, S, T, B, N, C
Input Resolution	16-bit
External Power Requirement	24 VDC
Includes	(1) BX-RTB10 screw terminal block kit
Programming Software	Do-more Designer programming software v2.1 or later
Additional Information	Optional BX-RTB10-1 or BX-RTB10-2 terminal block kits sold separately. Pre-wired ZIPLinks not available for temperature modules

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document