

# BX-08AD-1 Cut Sheet



BRX analog input module, 8-channel, current, 16-bit, input current signal range(s) of 0-20 mA, 4-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-08AD-1>

## Technical Specifications

<b>Brand</b>	BRX
<b>Item</b>	Input module
<b>I/O Module Type</b>	Analog
<b>Number Of Input Channels</b>	8
<b>Input Signal Type(s)</b>	Current
<b>Isolated Channels</b>	No
<b>Number of Non-Isolated Input Commons</b>	1
<b>Input Resolution</b>	16-bit
<b>Input Current Signal Range</b>	0-20 mA, 4-20 mA
<b>External Power Requirement</b>	24 VDC
<b>Requires</b>	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
<b>Programming Software</b>	Do-more Designer programming software v2.1 or later

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>