

BX-08AD-2B Cut Sheet



BRX analog input module, 8-channel, voltage, 16-bit, input voltage signal range(s) of 0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-08AD-2B>

Technical Specifications

Brand	BRX
Item	Input module
I/O Module Type	Analog
Number Of Input Channels	8
Input Signal Type(s)	Voltage
Isolated Channels	No
Number of Non-Isolated Input Commons	1
Input Resolution	16-bit
Input Voltage Signal Range	0-5 VDC, 0-10 VDC, +/- 5 VDC, +/- 10 VDC
External Power Requirement	24 VDC
Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.1 or later

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document