

BX-08CD3R Cut Sheet



BRX discrete combo module, Input: 4-point, 12-24 VDC, sinking/sourcing, Output: 4-point, 12-48 VDC/24-240 VAC, relay, (4) Form A (SPST) relays, 2A/point. Requires BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-08CD3R>

Technical Specifications

Brand	BRX
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	4
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Number of Non-Isolated Discrete Input Commons	1
Number of Output Points	4
Nominal Output Voltage	12-48 VDC/24-240 VAC
Discrete Output Type	Relay
Relay Configuration	(4) Form A (SPST) relays
Number of Non-Isolated Discrete Output Commons	1
Load Current	2A/point
Fuse Type	User-supplied external fuse
Requires	BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.0 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document