


BX-08NTC Cut Sheet



BRX temperature input module, thermistor, 8-channel, 16-bit resolution, input thermistor type(s): 2252, 10K-AN Type 3, 10K-CP Type 2, 5K, 3K and 1.8K ohm. (1) BX-RTB10 screw terminal block kit included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-08NTC>

Technical Specifications

Brand	BRX
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermistor
Number Of Channels	8
Input Thermistor Signal Types	2252, 10K-AN Type 3, 10K-CP Type 2, 5K, 3K and 1.8K
Input Resolution	16-bit
External Power Requirement	24 VDC
Includes	(1) BX-RTB10 screw terminal block kit
Programming Software	Do-more Designer programming software v2.3 or later
Additional Information	Optional BX-RTB10-1 or BX-RTB10-2 terminal block kits sold separately. Pre-wired ZIPLinks not available for temperature modules

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document