


# BX-08THM Cut Sheet



BRX temperature input module, thermocouple, 8-channel, 16-bit resolution, input thermocouple type(s): J, E, K, R, S, T, B, N, C. (1) BX-RTB10 screw terminal block kit included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-08THM>

## Technical Specifications

<b>Brand</b>	BRX
<b>Item</b>	Input module
<b>I/O Module Type</b>	Temperature
<b>Input Signal Type(s)</b>	Thermocouple
<b>Number Of Input Channels</b>	8
<b>Input Thermocouple Signal Type</b>	J, E, K, R, S, T, B, N, C
<b>Input Resolution</b>	16-bit
<b>External Power Requirement</b>	24 VDC
<b>Includes</b>	(1) BX-RTB10 screw terminal block kit
<b>Programming Software</b>	Do-more Designer programming software v2.3 or later
<b>Additional Information</b>	Optional BX-RTB10-1 or BX-RTB10-2 terminal block kits sold separately. Pre-wired ZIPLinks not available for temperature modules

## Agency Approvals

<b>UL Listed File #</b>	E139594
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BX-08THM.pdf>  
See store item page for other formats.