

# BX-08TRZ Cut Sheet



BRX relay output module, 8-point, 12-48 VDC/24-240 VAC, (8) Form A (SPST) no-suppression, 2 isolated common(s), 4 point(s) per common, 2A/point. Requires BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-08TRZ>

## Technical Specifications

<b>Brand</b>	BRX
<b>Item</b>	Output module
<b>I/O Module Type</b>	Relay
<b>Number of Output Points</b>	8
<b>Nominal Output Voltage</b>	12-48 VDC/24-240 VAC
<b>Relay Configuration</b>	(8) Form A (SPST) no-suppression relays
<b>Number of Isolated Commons</b>	2
<b>Jumper Selectable Isolation</b>	No
<b>Number of Points per Common</b>	4
<b>Load Current</b>	2A/point
<b>Fuse Type</b>	User-supplied external fuse
<b>Requires</b>	BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables
<b>Programming Software</b>	Do-more Designer programming software v2.8 or later

## Agency Approvals

<b>UL Listed File #</b>	E185989
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>