

BX-12NA Cut Sheet



BRX discrete input module, 12-point, 120-240 VAC, 3 isolated common(s), 4 point(s) per common. Requires BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-12NA>

Technical Specifications

Brand	BRX
Item	Input module
I/O Module Type	Discrete
Number of Input Points	12
Nominal Input Voltage	120-240 VAC
Fast Response	No
Number of Isolated Input Commons	3
Number of Points per Common	4
Requires	BX-RTB08, BX-RTB08-1 or BX-RTB08-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.0 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document