

BX-16CF3F2 Cut Sheet



BRX discrete combo module, Input: 8-point, 2-5 VDC, sinking/sourcing/TTL, Output: 8-point, 2-5 VDC, sourcing/TTL, 20 mA/point. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-16CF3F2>

Technical Specifications

Brand	BRX
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	2-5 VDC
Discrete Input Type	Sinking/sourcing/TTL
Number of Non-Isolated Discrete Input Commons	2
Number of Output Points	8
Nominal Output Voltage	2-5 VDC
Discrete Output Type	Sourcing/TTL
Number of Non-Isolated Discrete Output Commons	2
Load Current	20 mA/point
Fuse Type	User-supplied external fuse
Requires	BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables
Programming Software	Do-more Designer programming software v2.8 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document