

BX-16NB Cut Sheet



BRX discrete input module, 16-point, 12-24 VAC, 4 isolated common(s), 4 point(s) per common. Requires BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-16NB>

Technical Specifications

| | |
|---|---|
| Brand | BRX |
| Item | Input module |
| I/O Module Type | Discrete |
| Number of Input Points | 16 |
| Nominal Input Voltage | 12-24 VAC |
| Fast Response | No |
| Number of Isolated Input Commons | 4 |
| Number of Points per Common | 4 |
| Requires | BX-RTB10, BX-RTB10-1 or BX-RTB10-2 terminal block kit or ZIPLink pre-wired cables |
| Programming Software | Do-more Designer programming software v2.0 or later |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E185989 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |