

# BX-32ND3 Cut Sheet



BRX discrete input module, 32-point, 12-24 VDC, sinking/sourcing, 4 isolated common(s), 8 point(s) per common. Requires ZIPLink pre-wired cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-32ND3>

## Technical Specifications

|   |   |
|---|---|
| <b>Brand</b>                            | BRX   |
| <b>Item</b>                             | Input module  |
| <b>I/O Module Type</b>                  | Discrete  |
| <b>Number of Input Points</b>           | 32  |
| <b>Nominal Input Voltage</b>            | 12-24 VDC   |
| <b>Discrete Input Type</b>              | Sinking/sourcing                                    |
| <b>Fast Response</b>                    | No  |
| <b>Number of Isolated Input Commons</b> | 4   |
| <b>Number of Points per Common</b>      | 8   |
| <b>Requires</b>                         | ZIPLink pre-wired cable                             |
| <b>Programming Software</b>             | Do-more Designer programming software v2.3 or later |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E185989                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/BX-32ND3.pdf>  
See store item page for other formats.