

BX-DMIO-M-D Cut Sheet



BRX Do-more I/O controller, (1) Ethernet 10/100Base-T (RJ45) port(s), Do-more I/O controller protocol, up to 100 Mbps, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DMIO-M-D>

Technical Specifications

Brand	BRX
Item	Do-more I/O controller
Communication Port and Connection Type(s)	(1) Ethernet 10/100Base-T (RJ45)
Port Protocol(s)	Do-more I/O controller protocol
Port Speed(s)	up to 100 Mbps
External Power Requirement	24 VDC
Programming Software	Do-more Designer programming software v2.3 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-DMIO-M-D.pdf>
See store item page for other formats.