

BX-DMIO-M-D Cut Sheet



BRX Do-more I/O controller, (1) Ethernet 10/100Base-T (RJ45) port(s), Do-more I/O controller protocol, up to 100 Mbps, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-DMIO-M-D>

Technical Specifications

| | |
|---|---|
| Brand | BRX |
| Item | Do-more I/O controller |
| Communication Port and Connection Type(s) | (1) Ethernet 10/100Base-T (RJ45) |
| Port Protocol(s) | Do-more I/O controller protocol |
| Port Speed(s) | up to 100 Mbps |
| External Power Requirement | 24 VDC |
| Programming Software | Do-more Designer programming software v2.3 or later |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E185989 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |