

BX-MBIO-M Cut Sheet



BRX Modbus I/O controller, (1) Ethernet 10/100Base-T (RJ45) and (1) RS-485 (3-pin terminal) port(s), Modbus RTU and Modbus TCP/IP, up to 115.2k baud and up to 100 Mbps, external 120 VAC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-MBIO-M>

Technical Specifications

Brand	BRX
Item	Modbus I/O controller
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) RS-485 (3-pin terminal)
Port Protocol(s)	<ul style="list-style-type: none">• Modbus RTU• Modbus TCP/IP
Port Speed(s)	<ul style="list-style-type: none">• up to 115.2k baud• up to 100 Mbps
External Power Requirement	120 VAC

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-MBIO-M.pdf>
See store item page for other formats.