


BX-P-SER2-RJ12 Cut Sheet



BRX communication POM module, Do-more protocol, Modbus RTU and ASCII, 1 port, buffered, (1) RS-232 (RJ12) port(s). For use with all BRX MPUs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-P-SER2-RJ12>

Technical Specifications

Brand	BRX
Item	Communication POM module
Number of Ports	1
Buffered Ports	Yes
Communication Port and Connection Type(s)	(1) RS-232 (RJ12)
Port Protocol(s)	<ul style="list-style-type: none">• Do-more protocol• Modbus RTU Master/Slave• ASCII In/out• K-sequence Slave
Port Speed(s)	up to 115.2k baud
For Use With	All BRX MPUs
Programming Software	Do-more Designer programming software v2.0 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/BX-P-SER2-RJ12.pdf>
See store item page for other formats.