

# BX-SERIO Cut Sheet



BRX communication module, Do-more protocol, Modbus RTU and ASCII, 4 ports, buffered, (4) RS-232/RS-485 (3-pin terminal) port(s). For use with all BRX PLCs. (4) BX-RTB03S terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/BX-SERIO>

## Technical Specifications

<b>Brand</b>	BRX
<b>Item</b>	Communication module
<b>Number of Ports</b>	4
<b>Buffered Ports</b>	Yes
<b>Communication Port and Connection Type(s)</b>	(4) RS-232/RS-485 (3-pin terminal)
<b>Port Protocol(s)</b>	<ul style="list-style-type: none"><li>• Do-more protocol</li><li>• Modbus RTU Master/Slave</li><li>• ASCII In/out</li><li>• K-sequence Slave</li><li>• programming and monitoring</li><li>• DMX 512</li></ul>
<b>Port Speed(s)</b>	up to 115.2k baud
<b>For Use With</b>	All BRX PLCs
<b>Includes</b>	(4) BX-RTB03S terminal blocks
<b>Programming Software</b>	Do-more Designer programming software v2.5 or later

## Agency Approvals

<b>UL Listed File #</b>	E185989
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>