

C0-04AD-1 Cut Sheet



CLICK analog input module, 4-channel, current, 13-bit, input current signal range(s) of 0-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04AD-1>

Technical Specifications

Brand	CLICK
Item	Input module
I/O Module Type	Analog
Number Of Input Channels	4
Input Signal Type(s)	Current
Analog Input Type	Sinking
Isolated Channels	No
Input Resolution	13-bit
Input Current Signal Range	0-20 mA
External Power Requirement	24 VDC
Includes	Removable terminal block
Programming Software	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C0-04AD-1.pdf>
See store item page for other formats.