

C0-04AD-2 Cut Sheet



CLICK analog input module, 4-channel, voltage, 13-bit, input voltage signal range(s) of 0-10 VDC, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04AD-2>

Technical Specifications

| | |
|-----------------------------------|---|
| Brand | CLICK |
| Item | Input module |
| I/O Module Type | Analog |
| Number Of Input Channels | 4 |
| Input Signal Type(s) | Voltage |
| Analog Input Type | Sinking |
| Isolated Channels | No |
| Input Resolution | 13-bit |
| Input Voltage Signal Range | 0-10 VDC |
| External Power Requirement | 24 VDC |
| Includes | Removable terminal block |
| Programming Software | CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E157382 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C0-04AD-2.pdf>
See store item page for other formats.