

# C0-04DA-1 Cut Sheet



CLICK analog output module, 4-channel, current, 12-bit, output current signal range(s) of 4-20 mA, external 24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04DA-1>

## Technical Specifications

Brand	CLICK
Item	Output module
I/O Module Type	Analog
Number Of Output Channels	4
Output Signal Type	Current
Analog Output Type	Sourcing
Isolated Channels	No
Output Resolution	12-bit
Output Current Signal Range	4-20 mA
External Power Requirement	24 VDC
Includes	Removable terminal block
Programming Software	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

## Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>