

C0-04RTD Cut Sheet



CLICK temperature input module, RTD, 4-channel, 16-bit resolution, input RTD type(s): Pt100, Pt1000, JPt100, Cu10, Cu25 and Ni120. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04RTD>

Technical Specifications

Brand	CLICK
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	RTD
Number Of Channels	4
Input RTD Signal Types	Pt100, Pt1000, JPt100, Cu10, Cu25 and Ni120
Input Resistance Signal Range	0-3125 ohm, 0-1562.5 ohm, 0-781.25 ohm, 0-390.625 ohm and 0-195.3125 ohm
Input Resolution	16-bit
Includes	Removable terminal block
Programming Software	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document