

# C0-04RTD Cut Sheet



CLICK temperature input module, RTD, 4-channel, 16-bit resolution, input RTD type(s): Pt100, Pt1000, JPt100, Cu10, Cu25 and Ni120. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04RTD>

## Technical Specifications

<b>Brand</b>	CLICK
<b>Item</b>	Input module
<b>I/O Module Type</b>	Temperature
<b>Input Signal Type(s)</b>	RTD
<b>Number Of Channels</b>	4
<b>Input RTD Signal Types</b>	Pt100, Pt1000, JPt100, Cu10, Cu25 and Ni120
<b>Input Resistance Signal Range</b>	0-3125 ohm, 0-1562.5 ohm, 0-781.25 ohm, 0-390.625 ohm and 0-195.3125 ohm
<b>Input Resolution</b>	16-bit
<b>Includes</b>	Removable terminal block
<b>Programming Software</b>	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/C0-04RTD.pdf>  
See store item page for other formats.