

C0-04THM Cut Sheet



CLICK temperature input module, thermocouple, 4-channel, 16-bit resolution, input thermocouple type(s): J, E, K, R, S, T, B, N, C. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-04THM>

Technical Specifications

Brand	CLICK
Item	Input module
I/O Module Type	Temperature
Input Signal Type(s)	Thermocouple
Number Of Input Channels	4
Input Thermocouple Signal Type	J, E, K, R, S, T, B, N, C
Input Voltage Signal Range	0-1.25 VDC, 0-39.0625 mVDC, +/- 39.0625 mVDC, +/- 78.125 mVDC, 0-156.25 mVDC, +/- 156.25 mVDC
Input Resolution	16-bit
Includes	Removable terminal block
Programming Software	CLICK programming software v1.40 or later and CLICK CPU firmware v1.40 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C0-04THM.pdf>
See store item page for other formats.