


C0-08NE3 Cut Sheet



CLICK discrete input module, 8-point, 24 VAC/VDC, sinking/sourcing, 2 isolated common(s), 4 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-08NE3>

Technical Specifications

Brand	CLICK
Item	Input module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	24 VAC/VDC
Discrete Input Type	Sinking/sourcing
Fast Response	No
Number of Isolated Input Commons	2
Number of Points per Common	4
Includes	Removable terminal block
Programming Software	CLICK programming software v1.20 or later and CLICK CPU firmware v1.20 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document