


# C0-16TD1 Cut Sheet



CLICK discrete output module, 16-point, 5-27 VDC, sinking, 2 isolated common(s), 8 point(s) per common, 0.1A/point. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C0-16TD1>

## Technical Specifications

<b>Brand</b>	CLICK
<b>Item</b>	Output module
<b>I/O Module Type</b>	Discrete
<b>Number of Output Points</b>	16
<b>Nominal Output Voltage</b>	5-27 VDC
<b>Discrete Output Type</b>	Sinking
<b>Number of Isolated Output Commons</b>	2
<b>Number of Points per Common</b>	8
<b>Load Current</b>	0.1A/point
<b>Fuse Type</b>	User-supplied external fuse
<b>Includes</b>	Removable terminal block
<b>Programming Software</b>	CLICK programming software v1.00 or later and CLICK CPU firmware v1.00 or later

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>