

C18B-AP-2A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, metal, diffuse with background suppression, right-angle lens, 10-120mm sensing distance, light-on, PNP, potentiometer, 500 Hz switching frequency, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C18B-AP-2A>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 61.5mm body
IP Rating	IP67
Housing Material	Metal
Sensing Method	Diffuse with background suppression
Head Angle	Right-angle lens
Operating Voltage	10-36 VDC
Number of Wires	3
Switching Output	PNP
Sensing Distance	10-120mm
Sensitivity	Potentiometer
Operation Mode	Light-on
Switching Frequency	500 Hz
Light emission	Visible red
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	22 AWG
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document