

# C1FC10WE Cut Sheet



Hammond general purpose transformer, encapsulated core, 100 VA, 1-phase, 120/208/240/277 VAC primary, 120/240 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C1FC10WE>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Series</b>	Fortress
<b>Item</b>	Transformer
<b>Transformer Type</b>	General purpose
<b>Core Type</b>	Encapsulated
<b>Power Rating</b>	100 VA
<b>Number of Phases</b>	1
<b>Primary Voltage</b>	120/208/240/277 VAC
<b>Secondary Voltage</b>	120/240 VAC
<b>Frequency</b>	60 Hz
<b>Electrostatic Shield</b>	No
<b>NEMA Rating</b>	3R
<b>Mounting</b>	Wall

## Agency Approvals

<b>UL Listed File #</b>	E50394
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	3902
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>