

C1FC25XE Cut Sheet



Hammond general purpose transformer, encapsulated core, 250 VA, 1-phase, 190/200/208/220/240 or 380/400/416/440/480 VAC primary, 120/240 VAC secondary, 50/60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C1FC25XE>

Technical Specifications

Brand	Hammond
Series	Fortress
Item	Transformer
Transformer Type	General purpose
Core Type	Encapsulated
Power Rating	250 VA
Number of Phases	1
Primary Voltage	190/200/208/220/240 or 380/400/416/440/480 VAC

Secondary Voltage	120/240 VAC
Frequency	50/60 Hz
Fused	No
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Wall
Connection	Pigtail

Agency Approvals

UL Listed File #	E50394
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	3902
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/C1FC25XE.pdf>
See store item page for other formats.