


C2-08AR-6V Cut Sheet



CLICK PLUS discrete/analog combo module, Analog Input: 4-channel, voltage, Analog Output: 2-channel, voltage, Discrete Input: 4-point, Discrete Output: 4-point, relay, (4) Form A (SPST) relays.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C2-08AR-6V>

Technical Specifications

Brand	CLICK PLUS
Item	Combo module
I/O Module Type	Discrete/analog
Number of Analog Input Channels	4
Analog Input Signal Type	Voltage
Number of Non-Isolated Analog Input Commons	1
Number of Points per Analog Input Common	4
Input Resolution	12-bit
Input Voltage Signal Range	0-10 VDC
Number of Analog Output Channels	2
Analog Output Signal Type	Voltage
Number of Non-Isolated Analog Output Commons	1
Number of Points per Analog Output Common	2
Output Resolution	12-bit
Output Voltage Signal Range	0-10 VDC

Number of Discrete Input Points	4
Nominal Input Voltage	120 VAC
Number of Isolated Discrete Input Commons	1
Number of Points per Discrete Input Common	4
Number of Discrete Output Points	4
Nominal Output Voltage	6-240 VAC/6-27 VDC
Discrete Output Type	Relay
Relay Configuration	(4) Form A (SPST) relays
Number of Isolated Discrete Output Commons	1
Number of Points per Discrete Output Common	4
Load Current	1A/point
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	CLICK programming software v3.0 or later and CLICK CPU firmware v3.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document