


C2-14DR Cut Sheet



CLICK PLUS discrete combo module, Input: 8-point, 24 VDC, sinking/sourcing, Output: 6-point, 6-240 VAC/6-27 VDC, relay, (6) Form A (SPST) relays, 1A/point. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C2-14DR>

Technical Specifications

Brand	CLICK PLUS
Item	Combo module
I/O Module Type	Discrete
Number of Input Points	8
Nominal Input Voltage	24 VDC
Discrete Input Type	Sinking/sourcing
Number of Isolated Discrete Input Commons	2
Number of Points per Discrete Input Common	4
Number of Output Points	6
Nominal Output Voltage	6-240 VAC/6-27 VDC
Discrete Output Type	Relay
Relay Configuration	(6) Form A (SPST) relays
Number of Isolated Discrete Output Commons	2
Number of Points per Discrete Output Common	4/2
Load Current	1A/point

Fuse Type	User-supplied external fuse
Number of High-Speed Capable Input Points	8
High-Speed Counter(s)	up to (6) up counters, up to (6) down counters, up to (3) up/down counters, up to (4) pulse/direction (bi-directional) counters, up to (4) quadrature (A and B) counters, up to (2) quadrature (A and B with Z) counters
Interval Measurement	up to (6) single input (edge) timers, up to (3) dual input (dual edge) timers
Duration Measurement	up to (6) single input (edge) timers
Frequency Measurement	up to (6) single input up counters, up to (4) quadrature input (A and B) counters
Interrupt(s)	up to (8) input interrupts, up to (4) timer interrupts
Table-Driven Input(s)	up to (6) preset tables
Includes	Removable terminal block
Programming Software	CLICK programming software v3.0 or later and CLICK CPU firmware v3.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document