

C24025D Cut Sheet



NITRA pneumatic cylinder, compact, 1-1/2in bore, 5/8in rod diameter, 2 1/2in stroke, double acting, counter-bored holes mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/C24025D>

Technical Specifications

| | |
|-------------------------|---------------------|
| Brand | NITRA |
| Item | Cylinder |
| Working Fluid | Air |
| Cylinder Type | Compact |
| Bore Diameter | 1-1/2in |
| Stroke | 2 1/2in |
| Port Size | 1/8in female NPT |
| Mounting | Counter-bored holes |
| Action Type | Double acting |
| Body Material | Stainless steel |
| End Cap Material | Aluminum |
| Rod Material | Stainless steel |
| Rod Diameter | 5/8in |
| Rod Thread Size | 3/8-24 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |