C24025D Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA pneumatic cylinder, compact, 1-1/2in bore, 5/8in rod diameter, 2-1/2in stroke, double acting, counter-bored holes mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/C24025D

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Compact
Bore Diameter	1-1/2in
Stroke	2-1/2in
Port Size	1/8in female NPT
Mounting	Counter-bored holes
Action Type	Double acting

Magnetic Piston	No
Adjustable Cushions	No
Body Material	Stainless steel
End Cap Material	Aluminum
Rod Material	Stainless steel
Rod Diameter	5/8in
Rod Thread Size	3/8-24 UNF
Maximum Operating Pressure	200 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/C24025D.pdf
See store item page for other formats.